


# Big job? Make it EZ!

Save time and money with  
EZ Link modular devices!

# Arrow Hart

## Revolutionary Design

The EZ Link's thoughtful design allows for efficient, accurate and dependable installation.



## Features & Benefits

- 1. Sliding Installation**  
Unique sliding design allows the connector to simply slide into place faster and easier.
- 2. Guide Rails**  
Provide accurate and secure alignment during installation.
- 3. Arrow Design**  
The design easily identifies the direction to slide in the connector, providing safety against incorrect installation.
- 4. Release Wings**  
Wings provide an easy, one-hand release of the device, while providing two points of capture for connection retention.
- 5. Easy Labeling**  
A dedicated labeling area adds convenience for special labeling needs.
- 6. Wire Relief Slots**  
Allow sharp bending to make it easier to push all the wires back into the box during final installation.
- 7. Gripping Ridges**  
Tactile design incorporated into the connector provides a secure grip for the installers.

## The EZ Link Advantage

Arrow Hart EZ Link™ modular devices are the most efficient way to wire receptacles and switches for large commercial projects.



Duplex & TR receptacles

Controlled receptacles



Split circuit receptacles

### AVAILABLE IN THESE COLORS


\*For ordering devices, include Cat. no. followed by the color suffix, for example: TR5262\_\_



## Receptacles

### DESCRIPTION

2-pole, 3-wire grounding  
15A, 125V/AC  
20A, 125V/AC



### DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		NEMA	Description	Catalog no.	Color suffix
A	V/AC				
15	125	5-15R	<b>Duplex</b>	<input type="checkbox"/> EZ5262__	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ5362__	B, BK, GY, LA, RD, V, W
15	125	5-15R	<b>Decorator duplex</b>	<input type="checkbox"/> EZ6262__	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ6362__	B, BK, GY, LA, RD, V, W

### TAMPER RESISTANT DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		NEMA	Description	Catalog no.	Color suffix
A	V/AC				
15	125	5-15R	<b>Tamper resistant duplex</b>	<input type="checkbox"/> EZTR5262__	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR5362__	B, BK, GY, LA, RD, V, W
15	125	5-15R	<b>Tamper resistant decorator duplex</b>	<input type="checkbox"/> EZTR6262__	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR6362__	B, BK, GY, LA, RD, V, W

### HALF CONTROLLED DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		NEMA	Description	Catalog no.	Color suffix
A	V/AC				
15	125	5-15R	<b>Duplex</b>	<input type="checkbox"/> EZ5262CH__	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ5362CH__	B, BK, GN, GY, LA, RD, V, W
15	125	5-15R	<b>Decorator duplex</b>	<input type="checkbox"/> EZ6262CH__	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ6362CH__	B, BK, GN, GY, LA, RD, V, W
15	125	5-15R	<b>Tamper resistant duplex</b>	<input type="checkbox"/> EZTR5262CH__	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR5362CH__	B, BK, GN, GY, LA, RD, V, W
15	125	5-15R	<b>Tamper resistant decorator duplex</b>	<input type="checkbox"/> EZTR6262CH__	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR6362CH__	B, BK, GN, GY, LA, RD, V, W

### DUAL CONTROLLED DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		NEMA	Description	Catalog no.	Color suffix
A	V/AC				
15	125	5-15R	<b>Duplex</b>	<input type="checkbox"/> EZ5262CD__	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ5362CD__	B, BK, GN, GY, LA, RD, V, W
15	125	5-15R	<b>Decorator duplex</b>	<input type="checkbox"/> EZ6262CD__	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ6362CD__	B, BK, GN, GY, LA, RD, V, W
15	125	5-15R	<b>Tamper resistant duplex</b>	<input type="checkbox"/> EZTR5262CD__	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR5362CD__	B, BK, GN, GY, LA, RD, V, W
15	125	5-15R	<b>Tamper resistant decorator duplex</b>	<input type="checkbox"/> EZTR6262CD__	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR6362CD__	B, BK, GN, GY, LA, RD, V, W

### SPLIT CIRCUIT DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		NEMA	Description	Catalog no.	Color suffix
A	V/AC				
15	125	5-15R	<b>Duplex</b>	<input type="checkbox"/> EZ5262SC__	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ5362SC__	B, BK, GY, LA, RD, V, W
15	125	5-15R	<b>Decorator duplex</b>	<input type="checkbox"/> EZ6262SC__	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ6362SC__	B, BK, GY, LA, RD, V, W
15	125	5-15R	<b>Tamper resistant duplex</b>	<input type="checkbox"/> EZTR5262SC__	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR5362SC__	B, BK, GY, LA, RD, V, W
15	125	5-15R	<b>Tamper resistant decorator duplex</b>	<input type="checkbox"/> EZTR6262SC__	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR6362SC__	B, BK, GY, LA, RD, V, W

Compliances, specifications and availability are subject to change without notice.



Hospital Grade receptacles



GFCI receptacles



Toggle switches



Decorator switches

### AVAILABLE IN THESE COLORS

\*For ordering devices, include Cat. no. followed by the color suffix, for example: TR5262\_




## Receptacles

### DESCRIPTION

2-pole, 3-wire grounding  
15A, 125V/AC  
20A, 125V/AC

UL US NOM



### HOSPITAL GRADE DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		Description	Catalog no.	Color suffix
A	V/AC NEMA			
15	125 5-15R	Duplex	EZ8200_	B, BK, GY, LA, RD, V, W
20	125 5-20R		EZ8300_	B, BK, GY, LA, RD, V, W
15	125 5-15R	Decorator duplex	EZ8262_	B, BK, GY, LA, RD, V, W
20	125 5-20R		EZ8362_	B, BK, GY, LA, RD, V, W

### TAMPER RESISTANT HOSPITAL GRADE DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		Description	Catalog no.	Color suffix
A	V/AC NEMA			
15	125 5-15R	Tamper resistant duplex	EZTR8200_	B, BK, GY, LA, RD, V, W
20	125 5-20R		EZTR8300_	B, BK, GY, LA, RD, V, W
15	125 5-15R	Tamper resistant decorator duplex	EZTR8262_	B, BK, GY, LA, RD, V, W
20	125 5-20R		EZTR8362_	B, BK, GY, LA, RD, V, W

### SLIM GFCI RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		Description	Catalog no.	Color suffix
A	V/AC NEMA			
15	125 5-15R	Slim GFCI	EZGF15_	B, BK, GY, LA, RD, V, W
20	125 5-20R		EZGF20_*	B, BK, GY, LA, RD, V, W

### SLIM TAMPER RESISTANT GFCI RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		Description	Catalog no.	Color suffix
A	V/AC NEMA			
15	125 5-15R	Slim tamper resistant GFCI	EZTRGF15_	B, BK, GY, LA, RD, V, W
20	125 5-20R		EZTRGF20_*	B, BK, GY, LA, RD, V, W

\*FedSpec certification on 20A only

## Switches

### DESCRIPTION

Single pole, 3-way  
15A & 20A, 120/277V/AC



### TOGGLE SWITCHES, SEPARABLE TERMINAL TYPE


Rating		Description	Catalog no.	Color suffix
A	V/AC			
15	120/277	Single pole toggle	EZ1201_	B, BK, GY, LA, RD, V, W
20			EZ1221_	B, BK, GY, LA, RD, V, W
15	120/277	3-way toggle	EZ1203_	B, BK, GY, LA, RD, V, W
20			EZ1223_	B, BK, GY, LA, RD, V, W

### DECORATOR SWITCHES, SEPARABLE TERMINAL TYPE

Rating		Description	Catalog no.	Color suffix
A	V/AC			
15	120/277	Single pole decorator	EZ7601_	B, BK, GY, LA, RD, V, W
20			EZ7621_	B, BK, GY, LA, RD, V, W
15	120/277	3-way decorator	EZ7603_	B, BK, GY, LA, RD, V, W
20			EZ7623_	B, BK, GY, LA, RD, V, W

Compliances, specifications and availability are subject to change without notice.





## Connectors

### DESCRIPTION

2-pole, 3-wire receptacle connector  
20A, 125V/AC



Single pole, 3-wire switch connector  
3-way, 4-wire switch connector  
20A, 120/277VAC

### RECEPTACLE & SWITCH CONNECTORS

Description	Wire Type	Catalog no.	Color
Receptacle connector	Stranded	<input type="checkbox"/> EZRCSTR	Blue
Receptacle connector	Solid	<input type="checkbox"/> EZRC SOL	Blue
Switch single pole connector	Stranded	<input type="checkbox"/> EZSPSWSTR	Yellow
Switch single pole connector	Solid	<input type="checkbox"/> EZSPSW SOL	Yellow
Switch 3-way connector	Stranded	<input type="checkbox"/> EZ3WSWSTR	Yellow
Switch 3-way connector	Solid	<input type="checkbox"/> EZ3WSW SOL	Yellow

Compliances, specifications and availability are subject to change without notice.



Scan QR code to access our EZ Link video.



Scan QR code to access additional EZ Link resources.

Electrical Sector  
1123 Hwy 74 S  
Peachtree City, GA 30269  
United States  
Eaton.com  
Eaton.com/EZLink

Electrical Sector  
Canada Operations  
5925 McLaughlin Road  
Mississauga, Ontario, L5R 1B8  
Canada  
EatonCanada.ca  
Eaton.com/EZLink

Electrical Sector  
Mexico Operations  
Carr. Tlalnepantla -  
Cuautitlán Km 17.8 s/n  
Col. Villa Jardín esq.  
Cerrada 8 de Mayo  
Cuautitlán, Mexico CP 54800  
México  
Eaton.mx  
Eaton.com/EZLink