

Eaton 9PX UPS technical specifications (5 and 6 kVA models*)

Model overview

Catalog number	Power rating (VA/watts)	Input	Output	Dimensions (HxWxD, in.)**	Weight (lb.)
208V output,	50/60 Hz			•	
9PX5K	5000/4500	L6-30P***	(2) L6-30R, (2) L6-20R, Hardwired	5.1 (3U) x 17.3 x 28.4	106
9PX6K	6000/5400	L6-30P***	(2) L6-30R, (2) L6-20R, Hardwired	5.1 (3U) x 17.3 x 28.4	106
120/208V out	put, 50/60 Hz bun	dles			
9PX5KTF5 ¹	5000/4500	L6-30P***	(1) L6-30R, (2) L6-20R, (18) 5-20R, Hardwired	10.2 (6U) x 17.3 x 28.4	201
9PX5KP1	5000/4500	L6-30P	(1) L14-30R, (1) L6-30R, (6) 5-20R	10.2 (6U) x 17.3 x 28.4	203
9PX5KP2	5000/4500	Hardwired	Hardwired	10.2 (6U) x 17.3 x 28.4	201
9PX6KTF5 ¹	6000/5400	L6-30P***	(1) L6-30R, (2) L6-20R, (18) 5-20R, Hardwired	10.2 (6U) x 17.3 x 28.4	201
9PX6KP1	6000/5400	L6-30P	(1) L14-30R, (1) L6-30R, (6) 5-20R	10.2 (6U) x 17.3 x 28.4	203
9PX6KP2	6000/5400	Hardwired	Hardwired	10.2 (6U) x 17.3 x 28.4	201

^{*}Each module of every 9PX bundle ships with a 4-post rail kit. ***Terminal block with L6-30P cord.

Battery backup times (in minutes)****

	Internal				
Load (watts)	Batteries	+1 EBM	+2 EBMs	+3 EBMs	+4 EBMs
5400	3.0	16	28	47	58
4050	4.5	24	45	62	90
2700	8.5	38	71	104	133
1350	22.0	85	147	214	287
540	57.0	203	399	554	755

^{****}Runtimes are shown at full load with maximum power factor, are approximate and may vary with equipment, configuration, battery age, temperature, etc. View interactive runtime graphs at www.eaton.com/9PX.

Additional specifications

General				
Topology	Double-conversion online			
Configuration	Rack/tower			
Color	Black and silver			
Diagnostics	Full system self test at power up			
Warranty	3 years			
Rail kit	4-post rail kit and tower pedestals included; Optional 2-post rail kit available, part number: RK2PC			
Remote emergency power off (REPO)	ROO and RPO: Rear deck emergency stop connectors (for remote on/off and power off)			
Contents (Ships with the following items)	Network-M2 Web/SNMP card 4-post rail kit User manual Quick start guide Tower pedestals Intelligent Power Software Suite CD RS-232 serial cable			

Eaton.com/9PX TD153001EN July 2023

^{1.} Bundles with 9PXTFMR5 have output frequency of 60 Hz only

	USB cable		
	Cable gland for hardwire conection		
	Phillips head screw driver		
Electrical input	Fillinps nead screw driver		
Input voltage range	Full load: 176-276V, Derating: 100-276V		
Nominal voltage			
Default voltage	200/208/220/230/240V 9PX5K and 9PX6K: 208V		
Frequency Frequency range	50/60 Hz 60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz		
Input power factor Input current distortion	>.99 <5%		
•			
Circuit breaker Electrical output	(2) 20A for L6-20R		
	I 200/200/200/200/20//. F000 VA/AF00#-		
Power ratings NEMA 5 kVA	200/208/220/230/240V: 5000 VA/4500 watts		
Power ratings NEMA 6 kVA	230/240V: 5400 watts 220V: 5100 watts		
	208V: 4800 watts 200V: 4600 watts		
Power ratings IEC 6 kVA	200/208/220/230/240V: 6000 VA/5400 watts		
Nominal voltage	208V default (200/208/220/230/240V)		
Output voltage regulation	±1% steady-state		
Voltage THD	<pre></pre>		
Power factor	0.9		
Efficiency	93% with resistive load		
Transfer time	0 ms		
	UIIIS		
Battery Optional extended battery	I 9PXEBM180RT		
module (EBM)	SPAEDW100K1		
Maximum number of EBMs	Add up to 4 EBMs		
Battery description	Sealed, lead-acid; maintenance free		
Battery management	ABM technology; 3-stage charging extends battery service life by 50% and		
	provides advance warning for battery replacement		
Battery replacement	Hot-swappable internal batteries and EBMs		
Start on battery	Cold-start enabled; first cold start is always forbidden		
Communications	· · · · · · · · · · · · · · · · · · ·		
User interface	Graphical display. UPS status in a single view.		
LEDs	4 status-indicating LEDs		
Communication ports	RS-232 (RJ45) ports; USB port as standard (HID). 6-foot RS-232 and USB cables		
·	included		
Communications card slot	Network Card-M2 included		
Power management software	Eaton Intelligent Power Software Suite CD (included)		
Environmental & standards	· · · · · · · · · · · · · · · · · · ·		
RoHS compliance	Yes		
Surge protection	IEEE ANSI C62.41 Cat B2		
Heat dissipation (BTU/hr;	9PX5K: Online: 1150. Battery: 1560		
battery full charged, resistive	9PX6K: Online: 1245. Battery: 1895		
load)	<u> </u>		
Audiblenoise	<45 dB at 1 meter		
Operating temperature	0 to 40°C (32°F to 104°F)		
Safety conformance	CE / cULus / NOM		
EMC markings	kings IEC 62040-2:2006 Cat C2 / CISPR22 Class A / FCC part 15 Class A		
Storage temperature	0 to 35°C (32°F to 95°F); without batteries: -15 to 60°C (5°F to 140°F)		
Relative humidity	0 to 95% non-condensing		
Altitude	<1,000 meters for nominal power; 10% power derating every 1000 meters (up to		
	3000 meters) at 40°C		
	ment programs, specifications are subject to change without notice		

^{*}Due to continuing product improvement programs, specifications are subject to change without notice.