


Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:



TRGFH15W

AVAILABLE IN THESE COLORS

*For ordering devices, include Cat. no. followed by the color suffix, for example: GF15H_W

B	BK	GY	LA	RD	V	W
Brown	Black	Gray	Light Almond	Red	Ivory	White

MATERIALS

Housing	Top: Thermoplastic, Nylon (Standard and TR) PBT-PC (TWR) Bottom: Thermoplastic, PC
Strap	0.047" thick steel, zinc-plated
Line contacts	0.030" thick brass
Terminal	Brass/nickel-plated steel

SPECIFICATIONS

Electrical	Dielectric voltage: Withstands 2000V per UL 498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 100 cycles of overload @ 150% of rated current (DC) Trip time: 0.025 seconds (Class A) Frequency: 60 Hz; Voltage: 125V; Amperage: 15A/20A, 20A feed-through Short circuit testing: Meets and exceeds 10 kA Maximum interrupting capacity: 20 Amps
Testing & code compliance	cULus Listed to UL 498 and UL 943, file no. E60120 Meets all UL 943 (GFCI), UL 498 (receptacles) and applicable CSA requirements; NOM certified; Federal Specification W-C-596H for 20A models
Environmental	Flammability: Meets UL 94 requirements; V2 rated Temperature rating: -35°C to 66°C (-31°F to 150.8°F)
Mechanical	Terminal accommodation: #14 - 10 AWG Voltage ratings: Permanently marked on device

TRIP INDICATORS

EOL Indicator Light	RESET Button Light	Diagnosis
OFF	OFF	Branch circuit does not have power
OFF	ON (Green)	Device is functioning properly
OFF	ON (Red)	Device is in tripped state
Blinking or ON	ON (Red)	Device is in "end of life" state and must be replaced

 **Arrow Hart Website**
Buyer's Guide Product page

DESCRIPTION

2-pole, 3-wire grounding
15A, 125V/AC
20A, 125V/AC



HOSPITAL GRADE GFCI RECEPTACLES, BACK & SIDE WIRE

Rating		Description	Color suffix	Catalog no.
W	V/AC			
15	125	5-15R	RD, V, W	<input type="checkbox"/> GFH15__
20	125	5-20R	RD, V, W	<input type="checkbox"/> GFH20__*
15	125	5-15R	B, BK, GY, LA, RD, V, W	<input type="checkbox"/> TRGFH15__
20	125	5-20R	B, BK, GY, LA, RD, V, W	<input type="checkbox"/> TRGFH20__*
15	125	5-15R	W	<input type="checkbox"/> TWRGFH15__
20	125	5-20R	W	<input type="checkbox"/> TWRGFH20__*

Wallplate not included unless specifically stated; *FedSpec certification on 20A only.

APPLICATIONS

- Arrow Hart GFCI receptacles are UL Listed and fully compliant with all of the latest UL943 Class A GFCI and UL498 requirements
- Hospital Grade GFCIs are required by code in patient care areas near wet or damp locations

DESIGN FEATURES

- Slimmer design for easy installation, leaving more room for wires in the box
- Automatically self-tests periodically to ensure GFCI protection
- Child-safety black tamper resistant shutters help prevent improper insertion of foreign objects
- GFCIs incorporate lock-out functionality to protect against mis-wired line-load connections and GFCI circuitry damage
- Wider button wells for easy TEST and RESET
- "Always ON" Green LED indicating the device is functioning properly along with intuitive status indicators for trip and end of life states.
- Clean, modern industrial design with reduced top housing markings and neutral text direction on buttons
- Meets and exceeds 10 kA short circuit testing and Underwriters Laboratories (UL) UL943 safety standards
- Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure, provides redundant measure of ground continuity where jumper is used
- External backwire clamps provide visual confirmation of secure termination
- Line side terminals are backed out and staked for fast installation

COMPLEMENTARY PRODUCTS

Wallplates PJS26, PJS262

ADDITIONAL RESOURCES



Scan QR code for additional marketing collateral