


Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:



EZ5262SCW

#### AVAILABLE IN THESE COLORS

\*For ordering devices, include Cat. no. followed by the color suffix, for example: TR5262\_

<b>B</b>	<b>BK</b>	<b>GY</b>	<b>LA</b>	<b>RD</b>	<b>V</b>	<b>W</b>
Brown	Black	Gray	Light Almond	Red	Ivory	White

#### MATERIALS

<b>Housing</b>	Top: 8202 Nylon Bottom: 8202 Nylon
<b>Strap</b>	0.047" Thick galvanized steel
<b>Line contacts</b>	0.032" Thick brass C260
<b>Terminal</b>	0.032" Thick brass C260


#### SPECIFICATIONS

<b>Electrical</b>	<b>Dielectric voltage:</b> Withstands 2000V per UL 498 <b>Current interrupting:</b> Yes, at full-rated current <b>Temperature rise:</b> Max. 30°C (86°F) after Fed Spec Current Overload Test Procedure <b>Frequency:</b> 60 Hz; Voltage: 125V <b>Amperage:</b> 15A/20A <b>Maximum interrupting capacity:</b> 20 Amps
<b>Testing &amp; code compliance</b>	cULus Listed to UL 498 and file no. E15058 UL 498 (receptacles), applicable CSA requirements and NOM certified
<b>Environmental</b>	<b>Flammability:</b> Meets UL 94 requirements; V2 rated <b>Temperature rating:</b> -20°C to 60°C (-4°F to 140°F)
<b>Mechanical</b>	<b>Terminal accommodation:</b> With separable terminals use connectors EZRCSTR or EZRC SOL <b>Voltage ratings:</b> Permanently marked on device

 [Arrow Hart Website](#)  
[Buyer's Guide Product Page](#)

#### DESCRIPTION

**2-pole, 3-wire grounding**  
**15A, 125V/AC**  
**20A, 125V/AC**



#### SPLIT CIRCUIT DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		Description	Catalog no.	Color suffix
A	V/AC NEMA			
15	125 5-15R	<b>Duplex</b>	<input type="checkbox"/> EZ5262SC_	B, BK, GY, LA, RD, V, W
20	125 5-20R		<input type="checkbox"/> EZ5362SC_	B, BK, GY, LA, RD, V, W
15	125 5-15R	<b>Decorator duplex</b>	<input type="checkbox"/> EZ6262SC_	B, BK, GY, LA, RD, V, W
20	125 5-20R		<input type="checkbox"/> EZ6362SC_	B, BK, GY, LA, RD, V, W

#### SPLIT CIRCUIT TAMPER RESISTANT DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		Description	Catalog no.	Color suffix
A	V/AC NEMA			
15	125 5-15R	<b>Tamper resistant duplex</b>	<input type="checkbox"/> EZTR5262SC_	B, BK, GY, LA, RD, V, W
20	125 5-20R	<b>Tamper resistant duplex</b>	<input type="checkbox"/> EZTR5362SC_	B, BK, GY, LA, RD, V, W
15	125 5-15R	<b>Tamper resistant decorator duplex</b>	<input type="checkbox"/> EZTR6262SC_	B, BK, GY, LA, RD, V, W
20	125 5-20R	<b>Tamper resistant decorator duplex</b>	<input type="checkbox"/> EZTR6362SC_	B, BK, GY, LA, RD, V, W

#### APPLICATIONS

Leveraging Arrow Hart's existing feature-rich and high quality products, EZ Link split circuit receptacles have been designed to meet the requirements of commercial and industrial applications, while speeding up installation with a simple and convenient sliding termination type. EZ Link fulfills a need for customers who want to reduce project timelines through quick installation of wiring devices.

#### DESIGN FEATURES

- Intuitive arrow-shaped mating design and slim profile allows for rapid installation during trim-out
- Split circuit allows for control of one outlet through an attached traveler wire
- Connectors slide and lock into place on back of device, guided by precision rails and custom engineered wings resulting in unmatched connector retention
- Discrete connector designs prevent incorrect installations
- Tamper resistant receptacles comply with 2023 NEC Article 406.12

#### COMPLEMENTARY PRODUCTS

<b>Wallplates:</b>	PJS26, PJS262, PJS8
<b>EZ Link Connector:</b>	EZRCSTR, EZRC SOL

#### ADDITIONAL RESOURCES



Scan QR code for additional marketing collateral