


Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:



EZTR5362W

AVAILABLE IN THESE COLORS

*For ordering devices, include Cat. no. followed by the color suffix, for example: TR5262_



MATERIALS

Housing	Top: 8202 Nylon Bottom: 8202 Nylon
Strap	0.047" Thick galvanized steel
Line contacts	0.032" Thick brass C260
Terminal	0.032" Thick brass C260


SPECIFICATIONS

Electrical	Dielectric voltage: Withstands 2000V per UL 498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after Fed Spec Current Overload Test Procedure Frequency: 60 Hz; Voltage: 125V Amperage: 15A/20A Maximum interrupting capacity: 20 Amps
Testing & code compliance	cULus Listed to UL 498, file no. E15058 Meets all UL 498, Fed Spec W-C-596 testing standards, applicable CSA requirements and NOM certified
Environmental	Flammability: Meets UL 94 requirements; V2 rated Temperature rating: -20°C to 60°C (-4°F to 140°F)
Mechanical	Terminal accommodation: With separable terminals use connectors EZRCSTR or EZRCSOL Voltage ratings: Permanently marked on device

 [Arrow Hart Website](#)
[Buyer's Guide Product Page](#)

DESCRIPTION

2-pole, 3-wire grounding
15A, 125V/AC
20A, 125V/AC



TAMPER RESISTANT DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		Description	Catalog no.	Color suffix
A	V/AC			
15	125	5-15R Tamper resistant duplex	<input type="checkbox"/> EZTR5262_	B, BK, GY, LA, RD, V, W
20	125	5-20R Tamper resistant duplex	<input type="checkbox"/> EZTR5362_	B, BK, GY, LA, RD, V, W
15	125	5-15R Tamper resistant decorator duplex	<input type="checkbox"/> EZTR6262_	B, BK, GY, LA, RD, V, W
20	125	5-20R Tamper resistant decorator duplex	<input type="checkbox"/> EZTR6362_	B, BK, GY, LA, RD, V, W

APPLICATIONS

Leveraging Arrow Hart's existing feature-rich and high quality products, EZ Link tamper resistant receptacles have been designed to meet the requirements of commercial and industrial applications, while speeding up installation with a simple and convenient sliding termination type design. EZ Link fulfills a need for customers who want to reduce project timelines through quick installation of wiring devices.


DESIGN FEATURES

- Intuitive arrow-shaped mating design and slim profile allows for rapid installation during trim-out
- Child-safety black tamper resistant shutters help prevent improper insertion of foreign objects
- Connectors guided onto device by precision rails and retained in place by custom engineered wings resulting in unmatched connector retention
- Discrete connector designs prevent incorrect installations
- Complies with 2023 NEC Article 406.12

COMPLEMENTARY PRODUCTS

Wallplates: PJS26, PJS262, PJS8
EZ Link Connector: EZRCSTR, EZRCSOL

ADDITIONAL RESOURCES



Scan QR code for additional marketing collateral